



## BRIGHT GOLD LUSTRE 10%

Liquid gold and metallic lustres have a colloidal form and have a dark brown colour; they contain dissolved metals as a main component.

### PREPARATION - APPLICATION - FIRING

The products must be diluted with thinner #28271 in ranges from 5% to 15%.

They are mainly applied by brush on earthenware, glass, and porcelain. Airbrush application for professional use only. This application should always be on glazed objects; thoroughly clean and should be kept moisture free.

Firing temperatures:

Glass: 500°-600°C (Orton cone 022-021)

Earthenware: 690°-700°C (Orton cone 018)

Porcelain: 750°-815°C (Orton cone 017-015)

Before firing, allow items to sit in a dust-free, warm room for several hours to dry.

Color / Size	2 GR	5 GR	25 GR
Brilliant Gold 10%	28222	28220	28221