



COPPER LUSTRE

Liquid gold and metallic lustres have a colloidal form and have a dark brown colour; they contain dissolved metals as a main component.

PREPARATION - APPLICATION - FIRING

The products must be diluted with thinner #28271 in ranges from 5% to 15%.

They are mainly applied by brush on earthenware, glass, and porcelain. Airbrush application for professional use only. This application should always be on glazed objects; thoroughly clean and should be kept moisture free.

Firing temperatures:

Glass: 500°-600°C (Orton cone 022-021)

Earthenware: 690°-700°C (Orton cone 018)

Porcelain: 750°-815°C (Orton cone 017-015)

Before firing, allow items to sit in a dust-free, warm room for several hours to dry.

Color / Size

2 GR

5 GR

25 GR

Copper

28243

28241

28242