



SLIP CAST MOLD - CYLINDER VASE

Plaster mould in a cylindrical vase shape designed for producing hollow ceramic objects, suitable for both casting techniques (slip, liquid clay or SlipFast) and press moulding with plastic clay. The linear geometry ensures consistent wall thickness and repeatable results, making it ideal for batch production of decorative items and artistic ceramics.

Available in multiple diameters and heights. **Key features**

- Plaster mould for cylindrical vases
- Suitable for hollow objects
- Compatible with casting and press moulding
- Linear geometry for consistent results
- Ideal for batch production
- Wide range of diameters and heights

Technical specifications

- Material: special casting plaster
- Shape: cylindrical vase
- Compatible techniques: casting and pressing
- Variants: multiple diameters and heights

SKU F008164

INSTRUCTIONS

Instructions for use

Casting (slip / Slipfast)

- Dilute with water to reach the desired viscosity.
- Pour into the mould up to the brim and top up as needed.
- Leave for 10–30 minutes depending on thickness.
- Empty excess liquid (reusable after filtering) and allow to drain.
- Open the mould and remove the still workable piece.
- Dry for 12–24 hours, then fire or decorate.

Press moulding (plastic clay)

- Use clay with a firm, plastic consistency.
- Press clay into the mould evenly by hand.
- Compact thoroughly, avoiding air pockets.
- Trim excess material and level edges.
- Let rest briefly to aid release.
- Open mould and remove the piece while still workable.
- Allow to dry completely before finishing and firing.

SPECIFICHE

SKU	Size
47767	ø 70 x H. 300 MM
47768	ø 90 x H. 200 MM
47769	ø 140 x H. 300 MM